


## NMR 7WL SU Assembly


Call 800-321-7800 or visit us online at www.nookindustries.com to configure and order your NMR 7WL SU Assembly today!



Dimensions







Differences	
H [mm]	9
W2 [mm]	5.5
Wide Miniature Block Four Mounting Holes	0.0
(Runner Block) Details	
	7
Size [mm]	,
(Runner Block)Dimensions	
W [mm]	25
L [mm]	40.5
L1 [mm]	30.1
h2 [mm]	7.2
P1 [mm]	19
P2 [mm]	19
M × g2	M3 × 3
Ø [mm]	1.1
S [mm]	1.9
_ T [mm]	3.2
(Runner Block)Forces and Torques	
Basic Load Ratings C [N]	1570
Basic Load Ratings C0 [N]	3140
Static Moment Ratings-Ma [N-m]	14.9
Static Moment Ratings-Mb [N-m]	14.9
Static Moment Ratings-Mc [N-m]	22.7
(Runner Block)Weight	Eria i I
Weight-Block [g]	27
Wide Miniature Rail Top Mount Single Row	21
(Top Mount Rail)Details	
Size [mm]	7
(Top Mount Rail)Dimensions	
H [mm]	9
W1 [mm]	14
H1 [mm]	5.2
P [mm]	30
	5
D [mm]	
d1 [mm]	3.5
_g1 [mm]	3.5
(Top Mount Rail)Weight	
Weights-Rail [g/m]	516.0
Wide Miniature Rail Bottom Tapped Mount Single Row (Bottom Mount Rail)Details	
Size [mm]	7
(Bottom Mount Rail)Dimensions	<u>'</u>
H1 [mm]	7.5
W1 [mm]	
P [mm]	30
M1	M4 x 0.7
(Bottom Mount Rail)Weight	
Weights-Rail [g/m]	516.0